



Heavy Metals & Minerals Testing Kits

Heavy Metals and Minerals Testing Kits are designed for routinely analyzed heavy metals and minerals. All kits come with six, 30 mL standards which includes a nitric acid blank for easy dilution. Conveniently packaged in a sturdy, heavy-duty carton, these kits are perfect to store on a lab bench or in a cabinet. The 30 mL standards ship non-hazardous, saving money on shipping costs. The smaller volume also allows for less hazardous waste should the standard expire before its contents are used.

For additional product information, please visit www.eu.fishersci.com.

Heavy Metals Testing Kit				
Description	Concentration	Volume	Matrix	Part #
Arsenic (CLAS2-2M)	1,000 µg/mL	30 mL	2% HNO ₃	SPXHM-KIT
Cadmium (CLCD2-2M)	1,000 µg/mL		2% HNO ₃	
Chromium (CLCR2-2M)	1,000 µg/mL		2% HNO ₃	
Lead (CLPB2-2M)	1,000 µg/mL		2% HNO ₃	
Mercury (CLHG4-2M)	1,000 µg/mL		10% HNO ₃	
Nitric Acid Blank (CLBLK-HNO ₃ M)	—		—	
Minerals Testing Kit				
Description	Concentration	Volume	Matrix	Part #
Calcium (CLCA2-2M)	1,000 µg/mL	30 mL	2% HNO ₃	SPXMT-KIT
Iron (CLFE2-2M)	1,000 µg/mL		2% HNO ₃	
Magnesium (CLMG2-2M)	1,000 µg/mL		2% HNO ₃	
Potassium (CLK2-2M)	1,000 µg/mL		2% HNO ₃	
Sodium (CLNA2-2M)	1,000 µg/mL		2% HNO ₃	
Nitric Acid Blank (CLBLK-HNO ₃ M)	—		—	

CAN'T FIND THE STANDARDS YOU ARE LOOKING FOR?

SPEX Europe can make custom standards to meet your exact needs. Contact your Fisher Scientific Sales Representative for a quote.

CERTIFIED REFERENCE MATERIALS

Since 1954, SPEX Europe is the industry leader in the CRM marketplace meeting the needs of laboratories worldwide with innovation and research. Accredited by A2LA to ISO/IEC 17025:2017 & ISO 17034:2016. Certified by DQS to ISO 9001:2015.

Austria: +43(0)800-20 88 40 Belgium: +32 (0)56 260 260 Denmark: +45 70 27 99 20
 Germany: +49 (0)2304 9325 Ireland: +353 (0)1 885 5854 Italy: +39 02 950 59 478
 Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00
 Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303
 Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500